

Swagelok Tool Cases



- Swagelok Tools and Accessories conveniently packaged
- 1/4" - 1/2" and 6 - 12mm kits
- Master Installers Case and Compact Inspectors Case


Swagelok®

Australia | New Zealand

Components

Hand Tube Benders

Swagelok benders provide consistent, high-quality bends for tubing that is compatible with Swagelok tube fittings.



Features

- Available in 1/8, 1/4, 5/16, 3/8, 1/2 in., as well as 6, 8, 10, 12 mm tubing sizes
- Clevis handle design provides enhanced leverage for bends greater than 90°
- Roll dies reduce bending force and tube ovality, as compared to conventional slide block design
- 1 to 180° bending range

The hand tube bender cannot be used for SAF 2507 tubing over 1/4 in. or for medium-pressure tubing.

Thread Pitch Gauge

For use in conjunction with MS-13-77 Thread and End Connection Identification Guide



Gap Inspection Gauges

An excellent aid for verifying that a fitting has been properly tightened.



Swagelok

Australia | New Zealand

Preswaging Tool

A convenient accessory for Swagelok tube fitting installations in close quarters.



Features

- Preswages ferrules on the tube
- Enables the installer to work in a more open, safe area
- Makes it possible to complete the installation by following retightening instructions for Swagelok tube fittings

Tee Wrench

Provides backup support when installing Swagelok union tees and crosses.



Features

- Holds fitting body firmly and precisely
- Available in a variety of sizes
- Fits easily in tool box, pouch, or belt
- Head and handle made of stainless steel
- Features a cushioned vinyl grip and generous gripping area for handle
- Holds tee in various orientations

Snoop Leak Detector

Snoop liquid leak detector detects leaks in hard-to-reach areas.



Features

- Sustained bubble action works even on very small leaks and vertical surfaces.
- Flexible snoop tube extends for hard-to-reach areas.
- Noncorrosive, nonflammable formula does not contain chlorine.
- Contains corrosion inhibitor for added protection
- Formula dries clean, without staining.

Tube Cutters

The Swagelok tube cutter cuts stainless steel, soft copper, and aluminum tubing from 3/16 to 1 in. and 4 to 25 mm outside diameter. 1/16" & 1/8" cutter also available*.



*Third Party Warranty Applies

Features

- Flare-out and work hardening of tube end is reduced
- Knobs on handle are spaced in 1/8th turn increments to provide easy reference when advancing cutter wheel

Tube Deburring Tool

After using the tube cutter, Swagelok deburring tools deburr stainless steel, steel, and hard alloy tube ends.



Features

- For inside and outside diameters of 3/16 to 1 1/2 in. and 4 to 38 mm tubing
- Steel blades and durable die-cast housing for a long life

SWAK Teflon Sealant

- Lubricates threads, preventing costly thread damage due to galling
- Compatible with a wide range of chemicals



Teflon Tape

PTFE tape Pipe Thread Sealant, available in 1/4" and 1/2" widths



Features

- Material conforms to Commercial Item Description A-A-58092
- Temperatures up to 450°F (232°C)

Swagelok Australia & New Zealand Tool Cases

These strong cases are water and dust resistant. The Master Installers Case has free running wheels for easy transportation.

Carry all of your Swagelok tools in these rugged cases.

Available in Imperial and Metric sizes.

Both cases comes with extra storage compartment for your own spanners/tools.

Master Installers Case **MS-CASE-MI-IN** **(Imperial)**
 MS-CASE-MI-MM **(Metric)**



Master Installers Kit - Dimensions: 98cm x 47cm x 16cm Weight: 30kgs

Compact Inspectors Case **MS-CASE-CI-IN** **(Imperial)**
 MS-CASE-CI-MM **(Metric)**



Compact Inspectors Kit - Dimensions: 42cm x 33cm x 17cm Weight: 6kgs

Kits assembled for metric cases have 6mm, 10mm & 12mm tools and accessories in lieu of 1/4", 3/8" and 1/2"

**Master Installers Case Contents
(Imperial Case)**

Item	Description	Size	Part Number
-	Pelican Case - 1700	96.8 x 40.6 x 15.5 cm	-
1	Tube Fitters Manual	-	MS-13-03P
2	Tube Fitting Pocket Guide	-	MS-13-151
3	Hand Tube Bender Manual	-	MS-13-43
4	Thread ID Guide	-	MS-13-77
5	Gripper Pad	-	MS-07-25
6	Marker	-	MS-07-03
Tube Benders			
7	Hand Tube Bender	1/4"	MS-HTB-4T
8	Hand Tube Bender	3/8"	MS-HTB-6T
9	Hand Tube Bender	1/2"	MS-HTB-8
Gap Inspection Gauges			
10	Gap Inspection Gauge	1/4"	MS-IG-400
11	Gap Inspection Gauge	3/8"	MS-IG-600
12	Gap Inspection Gauge	1/2"	MS-IG-810
Wrenches / Pre-Swaging Tools			
13	Pre-Swaging Tool	1/4"	MS-ST-400GA
14	Pre-Swaging Tool	3/8"	MS-ST-600GA
15	Pre-Swaging Tool	1/2"	MS-ST-810GA
16	Tee Wrench	1/4"	MS-TW-4
17	Tee Wrench	3/8"	MS-TW-6
18	Tee Wrench	1/2"	MS-TW-8
Tube Prep Tools / Accessories			
19	Snoop Leak Detector	-	MS-SNOOP-80Z
20	Tube Cutter	3/16" - 1"	MS-TC-308
21	Tube Cutting Wheel	-	MS-TCW-308
22	Tube Deburring Tool	3/16" - 1 1/2"	MS-TDT-24
23	Thread Pitch Gauge	-	MS-TIK-PG
24	1/4" Teflon Tape	1/8 - 3/8"	MS-STR-4
25	1/2" Teflon Tape	1/2" +	MS-STR-8

**Compact Inspectors Case Contents
(Imperial Case)**

Item	Description	Size	Part Number
-	Pelican Case - 1450	40.6 x 33 x 17.4 cm	-
1	Tube Fitting Pocket Guide	-	MS-13-151
2	Thread ID Guide	-	MS-13-77
3	Gripper Pad	-	MS-07-25
4	Marker	-	MS-07-03
Gap Inspection Gauges			
5	Gap Inspection Gauge	1/4", 3/8", 1/2"	MS-IG-468
Wrenches / Pre-Swaging Tools			
6	Pre-Swaging Tool	1/4"	MS-ST-400GA
7	Pre-Swaging Tool	3/8"	MS-ST-600GA
8	Pre-Swaging Tool	1/2"	MS-ST-810GA
Tube Prep Tools / Accessories			
9	Spare Nuts & Ferrules Case*	*Consists of	CS-TRAY
	10 x Ferrule Sets	1/4"	SS-400-SET
	10 x Ferrule Sets	3/8"	SS-600-SET
	10 x Ferrule Sets	1/2"	SS-810-SET
	5 x Swagelok Nuts	1/4"	SS-402-1
	5 x Swagelok Nuts	3/8"	SS-602-1
	5 x Swagelok Nuts	1/2"	SS-812-1
10	Snoop Leak Detector	-	MS-SNOOP-80Z
11	Tube Cutter	3/16" - 1"	MS-TC-308
12	Tube Deburring Tool	3/16" - 1 1/2"	MS-TDT-24
13	Thread Pitch Gauge	-	MS-TIK-PG
14	1/4" Teflon Tape	1/8 - 3/8"	MS-STR-4
15	1/2" Teflon Tape	1/2" +	MS-STR-8



Australia | New Zealand



Australia | New Zealand

Warranty Information

Swagelok products are backed by The Swagelok Limited Lifetime Warranty. For a copy, visit swagelok.com or contact your authorised Swagelok representative.

Carry Cases and foam inserts are excluded from this warranty.

Swagelok Australia & New Zealand

anz.swagelok.com

Melbourne

42 Metrolink Circuit
Campbellfield
Victoria 3061
Tel: +61 3 9303 2100

Brisbane

Unit 11 / 441 Nudgee Road
Hendra
Queensland 4011
Tel: +61 7 3632 0800

Auckland

111c Kerwyn Avenue
East Tamaki 2013
Tel: +64 9 273 2720

Sydney

1/72-74 Woodfield Boulevard
Caringbah
Sydney 2229
Tel: +61 2 9526 6155

Freecall NZ:

0800 792 435 (0800 SWAGELOK)

New Plymouth

1 Davidson Street
New Plymouth 4340
Tel: +64 6 759 9370

Adelaide

5A Sleaford Road
Windsor Gardens SA 5087
Tel: +61 8 8369 0899

Gippsland

1 / 396 Raymond Street
Sale
Victoria 3853
Tel: +613 5144 7733

Perth

2 Barrel Way
Canning Vale WA 6155
Tel: +61 8 9331 1111