UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT NOVA SCOTIA YUKON

PRINCE EDWARD ISLAND NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Swagelok Company	
MANUFACTURERS ADDRESS: 29500 Solon Road Solon Obje 44120 Lts	ZA
Headquarters, 29500 Solon Road, Solon Objo 441	30 IISA (See Attachment A)
SALESSATIST THINGS TO BE REGISTERED, CIRCLE ONE CATEGOR	RY ONLY TITLE OF THE STANDARD OF CONSTRUCTION
A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or redu B Flanges: all flanges © Valves: all flanges D Expansion joints, flexible connections, and flose assemblies: all types E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Cartifled capacity-rated pressure relief devices acceptable as primary over pressure boilers, pressure vessets, piping and fuelible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 □ Class 2 □ Class 3 □, (Meeting AECB or ASME	ASME B31.1 and ASME B31.3 (for unlisted components)
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR O	
Swagelok	FORGED D WELDED D WROUGHT M CAST D OTHER D DESCRIBE OTHER:
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUA	LITEMS TO BE REGISTERED.
DECLARATION: David H. Peace teaceta is employed by Swarpelok Come	
responsibility for the quality of the end product do solemnly declare that the infinity knowledge represents the product for which registration is sought. The direct temperature ratings, and identification markings are in accordance with the her manufacture of these fittings is regulated by a Quality Control Program which earlied by BSI as be declaration conscientiously believing it to be true, and knowing that it is of the solection of Declarer;	ormation contained in this form is true and to the best of tensions, materials of construction, pressure rein named standards. I further declare that the extends to each plant where fabrication occurs in whole long sulfable for that purpose and imake this section.
This 1 2011 day of March AD OD to James Like	thu 主要的一次,在我们与解释的
or Notary Public: (sign) (Affix Official seal to the right)	ato of Ohlo. es: 01/08/2019 NU(V/WE)\$
This space for Regulatory Auth This registration must be revalidated after ten (10) ye	orificing and the state of accompanse
CRN: 0C18622.5	REGIS LLNED
FID#: 1214	CRN OC 18622,57
Notes: 1. All fittings shall be registered in the name of the Manufacturer. 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation. 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product. 4. Quality control programs shall be resubmitted for validation.	Signed Sept 16,2016 Signed Short May A
at a maximum interval of five (5) years,	Territorial Régistration Fee

Attachment B. Scope of Registration for Swagelok VB03 and VB04 Series Process Interface Valves (Category C)

Product Scope

This document represents the scope of Swagelok VB03 and VB04 Series Process Interface Valves covered by this submission for CRN approval. Swagelok VB03 and VB04 Series Process Interface Valves were designed and evaluated in accordance with ASME B31.1 and ASME B31.3 as unlisted components.

Summary Tables

	Table 1: VB03 Scope									
Body Material/ Specification	Configuration	ASME Class	Flange Size	Bore Size	Minimum Temperature	Maximum Allowable Working Pressure (psig)				
		Oldos			remperature	At 70°F	At 400°F			
F316/F316L ASTM A182	Ball/Needle/Ball (Block/Bleed/Block): Full Bore Reduced Bore	150 300 600 900	1 in. (DN 25) 1-1/2 in. (DN 40) 2 in. (DN 50)	1 in. (DN 25) 1-1/2 in. (DN 40)	-58°F	2160	1540			

1) All seat and seal combinations

2) All flange types: RF smooth, RF serrated, and RTJ

3) Outlet connection = same as process

4) Bleed connection: 1/2 in. female NPT

	Table 2: VB04 Scope									
Body Material/ Specification	Configuration	ASME Class	Process Connection Size	Process Connection	Outlet Connection	Minimum Temperature	Maximum Allowable Working Pressure (psig) At At 70°F 400°F			
F316/F316L ASTM A182	Ball/Needle/Ball (Block/Bleed/Block):	150	1/2 in. (DN 15)	Flange – RF Smooth	1/2 in. female NPT Flange	-58°F				
	3/8 in. (9.5 mm) bore	300 / 600	3/4 in. (DN 20) 1 in. (DN 25)	Flange – RF Serrated			3600	2570		
	1/2 in. (14 mm) bore	900 /	1-1/2 in. (DN 40)	Flange – RTJ						
	3/4 in. (20 mm) bore	1500	2 in. (DN 50)	NPT Female (1/2 DN 15 only)						


1) All seat and seal combinations

2) Bleed connection: 1/2 in. female NPT

Product Drawings/Configurations

Process Interface Valves





Page 2 of 3

Typical Product Characteristics:

The list below are examples of product options which do not affect the pressure-temperature ratings shown in the Summary Table. All of the following options are within the scope of this registration:

- Lockable Lever Handles (for block valves)
- Non-lockable Lever Handles (for block valves)
- Antitamper bleed valve
- Bar handle (for bleed valve)
- Injection and Sampling probes
- Integral Check valves
- Sour gas service

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

Special Ordering Instructions

None

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

Swagelok Process Interface Valves MS-02-340, R9