

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: <u>Swagelok Company</u>	
MANUFACTURERS ADDRESS: <u>29500 Solon Road, Solon, Ohio 44139 USA</u>	
PLANT LOCATIONS: <u>Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A)</u>	
<p align="center">CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY</p> <p>A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers B Flanges: all flanges C Valves: all line valves D Expansion joints, flexible connections, and hose assemblies: all types E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> (Meeting AECB or ASME requirements)</p>	<p align="center">TITLE OF THE STANDARD OF CONSTRUCTION</p> <p>ASME B31.1 for unlisted components, ASME B31.3 for unlisted components</p>
<p align="center">SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT</p> <p align="center" style="font-size: 2em;">Swagelok</p>	<p align="center">TYPE OF CONSTRUCTION</p> <p>FORGED <input type="checkbox"/> WELDED <input type="checkbox"/> WROUGHT <input checked="" type="checkbox"/> CAST <input type="checkbox"/> OTHER <input type="checkbox"/> DESCRIBE OTHER:</p>
<p align="center">LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:</p> <p>ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents</p>	

DECLARATION:

I Joel Feldman, Vice President, Engineering (see note 3) employed by Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by BSI as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: [Signature]

Declared before me at Solon, Ohio

This 18th day of July AD 2019

Commissioner of Oaths
or Notary Public: (sign) Brenda Hammel

(Affix Official seal to the right)

USE THIS SPACE FOR
OFFICIAL SEAL



<p align="center">This space for Regulatory Authority use This registration must be revalidated after ten (10) years from the date of registration.</p> <p>CRN: <u>0C21782.5</u></p> <p>FID#: <u>1214</u></p> <p>SO SERIES LIFT CHECK VALVES - 1/8" - 1" d" Notes: up to 6000 psi - 55</p> <ol style="list-style-type: none"> All fittings shall be registered in the name of the Manufacturer. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation. The declaration shall be made by the person having full authority and responsibility for the quality of the end product. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years. <p>CRN EXPIRES SEPT. 15, 2029</p>	<p align="center">Brunswick</p> <p align="center">DEPT OF JUSTICE PUBLIC SAFETY BOILER & PRESSURE VESSEL ACT</p> <p align="center">REGISTRATION ONLY</p> <p align="center">CRN <u>0C21782.57</u></p> <p align="center"><u>[Signature]</u> CHIEF BOILER INSPECTOR</p> <p align="center">DATE <u>10/18/2019</u></p> <p><input type="checkbox"/> BLRs <input type="checkbox"/> PVs <input checked="" type="checkbox"/> FITTINGS <input type="checkbox"/> NUCLEAR COMPONENTS</p>
--	--

Attachment B: Scope of CRN Registration for Swagelok 50 Series Lift Check Valves (Category C)


This document represents the scope of the 50 Series Lift Check Valves covered by this submission for CRN approval. The Swagelok 50 Series Lift Check Valves were designed and evaluated in accordance with ASME B31.1-2016 for unlisted components and ASME B31.3-2016 for unlisted components.

Summary Table

Product Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure		Design Code of Construction
				At -65 to 100°F	@ max temperature	
53	Body	Stainless Steel (ASTM A479)	Swagelok Tube Fitting 1/8", 1/4", 6MM, 8MM Female NPT 1/8", 1/4" Male NPT 1/4" Tube Socket Weld 1/4"	6000 psi @ 100°F	3280 psi @ 900°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
56	Body	Stainless Steel (ASTM A479)	Swagelok Tube Fitting 3/8", 1/2", 10MM Female NPT 1/4" Tube Socket Weld 3/8" Tube Socket Weld 1/2"	6000 psi @ 100°F	3280 psi @ 900°F	
58	Body	Stainless Steel (ASTM A479)	Swagelok Tube Fitting 1/2", 12MM, 14MM Male NPT 1/2" Tube Socket Weld 1/2"	6000 psi @ 100°F	3280 psi @ 900°F	
			Swagelok Tube Fitting 3/4"	5800 psi @ 100°F	3280 psi @ 900°F	
			Swagelok Tube Fitting 1"	4700 psi @ 100°F	3280 psi @ 900°F	
			Swagelok Tube Fitting 16MM	5805 psi @ 100°F	3280 psi @ 900°F	
			Swagelok Tube Fitting 20MM	5510 psi @ 100°F	3280 psi @ 900°F	
			Swagelok Tube Fitting 25MM	4640 psi @ 100°F	3280 psi @ 900°F	
			Female NPT 3/8"	5300 psi @ 100°F	3048 psi @ 900°F	
			Female NPT 1/2"	4900 psi @ 100°F	2818 psi @ 900°F	
			Female NPT 3/4"	4600 psi @ 100°F	2645 psi @ 900°F	

THIS IS PART OF
 CRN 0021782.5
 Technical Standards & Safety Authority
 Boilers & Pressure Vessels
 Safety Program

Product Illustration




Quality System

The Swagelok Company quality system complies with the requirements of EN ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

- 50 Series Lift Check Valves Catalog MS-01-098, R10



Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man

THIS IS PART OF
CRN 0021782.5
 Technical Standards & Safety Authority
 Gases & Pressure Vessels
 Safety Program