

Statutory Declaration (Registration of Fittings)

TSK-1008

I. Declaration Information

I, Joel Feldman
Vice President, Engineering
(company title, e.g. vice president, plant manager, chief engineer)
(must be in a position of authority in the manufacturing plant where the fitting is produced)
of: Swagelok Company
(name of manufacturer)

In this space, show facsimile of manufacturer's logo or trademark as it will appear on the fitting.



located at: Headquarters: 29500 Solon Road Solon, Ohio 44139 USA
(Plant Address - Apt/Street) (City, Prov) (Postal Code)

do solemnly declare that the fittings listed hereinunder, which are subject to the **Saskatchewan Boiler and Pressure Vessel Safety Act** (check one)

- Comply with the requirements of ASME B31.1 and ASME B31.3 which specifies the dimensions, (title of recognized North American Standard) Materials of construction, pressure / temperature ratings and identification marking of the fittings, or
- Are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with _____ as supported by the attached data which identifies the dimensions, materials of construction, pressure / temperature ratings and the basis for such ratings, and the marking of the fittings for identification.

I further declare that the manufacturer of these fittings is controlled by a quality control program which has been verified by the following authority, BSI as being suitable for the manufacturer of these fittings to the stated standard. The fittings covered by this declaration, for which I seek registration, are Category C. Valve

In support of this application, the following information, calculations and / or test data are attached:

ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents

II. Declaration

DECLARED before me at Solon In the State of Ohio
this 21st day of Nov, 2019
Brenda Hammel (print name) Joel C. Feldman (Signature)
Brenda Hammel (Signature of Commissioner of Oaths)

III. Office Use Only

To the best of my knowledge and belief, the applicant is qualified to apply for registration under the **Saskatchewan Boiler and Pressure Vessel Safety Act** and is accepted for registration.

(Registration Number)



**Technical
Safety Authority
of Saskatchewan**

Registration No. OC22234.53
File No. 11452
Registered
Date: April 29, 2020
Expiry Date: March 10, 2030

Codes & Standards Compliance Office



Attachment B: Scope of Registration for Swagelok O, 1, 18, 20 and 26 Series Integral Bonnet Needle Valves (Category C)

This document represents the scope of the Swagelok O, 1, 18, 20 and 26 Series Needle Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

Summary Table

Product Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections, Sizes	Maximum Rated Pressure (psig)		Design Code of Construction
				At -65 to 100°F (except Carbon Steel)	@ max. temperature	
O, 1, 18	Body	F316 SS (ASTM A182)	Tube Fitting 1/8", 1/4", 3/8", 1/2", 3/4", 3MM, 6MM, 8MM, 10MM, 12MM, 18MM Female NPT 1/8", 1/4" Male NPT 1/8", 1/4", 3/8" Female ISO 1/4"	5000	3130 @ 600°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
			Female NPT 3/8", 1/2" Female ISO 3/8", 1/2" Male NPT 1/2"	4400	2770 @ 600°F	
20, 26	Body	F316 SS (ASTM A479)	Tube Fitting 1/4", 3/8", 1/2" Female NPT 1/4" Male NPT 1/4" 3/8", 1/2", 3/4" Female ISO 1/4"	6000	3760 @ 600°F	
			Female NPT 3/8"	5300	3330 @ 600°F	
			Female NPT 1/2" Female ISO 1/2"	4900	3080 @ 600°F	
1, 18	Body	Type 1137 Carbon Steel (ASTM 181)	Tube Fitting 1/4", 3/8", 1/2", 3/4", 6MM, 8MM, 10MM, 12MM, 18MM Female NPT 1/4", 3/8", 1/2" Male NPT 1/4", 3/8", 1/2" Female ISO 1/4", 3/8", 1/2"	3000 @ -20°F to 100°F	2615 @ 350°F	
O, 1	Body	Alloy 400 (ASTM B564)	Tube Fitting 1/8", 1/4", 3/8", 1/2", 3/4", 8MM, 10MM Female NPT 1/8", 1/4" Male NPT 1/8", 1/4", Female ISO 1/4"	3000	2375 @ 500°F	



Product Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure (psig)		Design Code of Construction
				At -65 to 100°F	@ max. temperature	
O, 1, 18	Body	Brass C37700 (ASTM B283)	Tube Fitting 1/8", 1/4", 6MM Female NPT 1/8", 1/4" Female ISO 1/4" Male NPT 1/8", 1/4", 1/2"	3000	2350 @ 200°F	ASME B31.1 (Unlisted Components)
			Tube Fitting 3/8"	2200	1760 @ 200°F	
			Tube Fitting 1/2"	2100	1680 @ 200°F	
			Tube Fitting 3/4"	1800	1440 @ 200°F	
			Tube Fitting 8MM	2320	1858 @ 200°F	
			Tube Fitting 10MM	1885	1509 @ 200°F	
			Tube Fitting 12MM	2030	1625 @ 200°F	
			Tube Fitting 18MM	1590	1277 @ 200°F	
			Female NPT 3/8" Female ISO 3/8"	2600	2340 @ 200°F	
			Female NPT 1/2" Female ISO 1/2"	2400	2160 @ 200°F	
			Tube Fitting 1/8", 1/4", 6MM Female NPT 1/8", 1/4" Female ISO 1/4" Male NPT 1/8", 1/4", 1/2"	3000	390 @ 400°F	ASME B31.3 (Unlisted Components)
			Tube Fitting 3/8"	2200		
			Tube Fitting 1/2"	2100		
			Tube Fitting 3/4"	1800		
			Tube Fitting 8MM	2300		
			Tube Fitting 10MM	1885		
			Tube Fitting 12MM	2030		
			Tube Fitting 18MM	1590		
Female NPT 3/8", 1/2" Female ISO 3/8", 1/2"	2400					

Product Illustrations



Configurations

Bodies are available in straight pattern and angle pattern.

Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

Stem Packing Options

Polytetrafluoroethylene (PFA)
Ultra High Molecular Weight Polyethylene (UHMWPE)
Polyetheretherketone (PEEK)

O-ring Stem Seal Options

Nitrile
Ethylene Propylene
Silicone
Kalrez

Stem Designs

Regulating
PCTFE soft-seat regulating
PTFE soft-seat regulating

Additional options and non-pressure boundary alterations that do not affect pressure-temperature ratings may be made available within the scope of this registration. Examples of these would include handle options, actuator options, etc.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

- O, 1, 18, 20 and 26 Series Needle Valve Catalog MS-01-164, Rev N

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man



Registration No. OC22234.53

File No. 11452

Registered

Date: April 29, 2020

Expiry Date: March 10, 2030

Codes & Standards Compliance Office