

THE NETHERLANDS  
(N E D E R L A N D)

## EC TYPE-APPROVAL CERTIFICATE

Communication concerning:

- EC type-approval <sup>(1)</sup>
  - ~~extension of EC type approval~~ <sup>(1)</sup>
  - ~~refusal of EC type approval~~ <sup>(1)</sup>
  - ~~withdrawal of EC type approval~~ <sup>(1)</sup>
- } of a type of  
hydrogen component

with regard to Regulation (EC) number 79/2009, as implemented by Regulation (EU) number 406/2010.

EC type-approval number : e4\*79/2009\*406/2010\*0033\*00

Reason for extension : N.A.

## SECTION I

- 0.1. Make (trade name of manufacturer) : Swagelok Company
- 0.2. Type : Excess flow valve XS series
- 0.3. Means of identification of type, if marked on the component <sup>(2)</sup> : SS-XSS6mm  
: SS-XSS4  
: SS-XSF4
- 0.3.1. Location of that marking : Body of the component (see drawing)
- 0.5. Name and address of manufacturer : Swagelok Company  
29500 Solon Road 44139  
Solon, Ohio  
United States of America
- 0.7. In the case of components and separate technical units, location and method of affixing of the EC approval mark : On the sample



**Approval number: e4\*79/2009\*406/2010\*0033\*00**

- 0.8. Name(s) and address(es) of assembly plant(s) : Swagelok Company  
Order Fulfillment Center (OFC)  
29495 FA Lennon Drive  
Solon, OH 44139
- 0.9. Name and address of manufacturer's representative (if any) :

SECTION II

1. Additional information (where applicable) : see Addendum
2. Technical service responsible for carrying out the tests : Kiwa Nederland B.V.  
P.O.Box 137  
7300AC Apeldoorn  
The Netherlands
3. Date of test report : 06-08-2020
4. Number of test report : 191101448
5. Remarks (if any) : see Addendum
6. Place : Zoetermeer
7. Date : 21 October 2020
8. Signature :



R.F.R. Clement

- Attachments:
- Information package.
  - Test report.

---

<sup>(1)</sup> Delete where not applicable.

<sup>(2)</sup> If the means of identification of type contains characters not relevant to describe the vehicle, component or separate technical unit types covered by this information document, such characters shall be represented in the documentation by the symbol '?' (e.g. ABC??123??).

ADDENDUM

to EC type-approval certificate number: e4\*79/2009\*406/2010\*0033\*00

relating to EC component type-approval of a hydrogen component or system

1. Additional information

1.1. Hydrogen system designed to use liquid hydrogen/Hydrogen system designed to use compressed (gaseous) hydrogen/Hydrogen component designed to use liquid hydrogen/Hydrogen component designed to use compressed (gaseous) hydrogen <sup>(1)</sup>

2. Specifications and test results

2.1. Containers designed to use compressed (gaseous) hydrogen

2.1.1. Container material specifications

Material specifications	Applicable to material						Details
	Steel	Aluminium alloy	Plastic liner	Fibre	Resin	Coating	
Material manufacturer	✓	✓	✓	✓	✓		
Type of material	✓	✓	✓	✓	✓		
Material identification	✓	✓	✓	✓	✓		
Heat treatment definition	✓	✓					
Chemical composition	✓	✓					
Cold or cryoforming procedure	✓						
Welding procedure definition	✓	✓					

2.1.2. Container material test results

Material test	Applicable to material						Specified material value	Test value
	Steel	Aluminium alloy	Plastic liner	Fibre	Resin	Coating		
Tensile test	✓	✓	✓					
Charpy impact test	✓							
Bend test	✓	✓						
Macroscopic examination	✓							



Material test	Applicable to material						Specified material value	Test value
	Steel	Aluminium alloy	Plastic liner	Fibre	Resin	Coating		
Corrosion test		√						
Sustained load cracking test		√						
Softening temperature test			√					
Glass transition temperature test					√			
Resin shear strength test					√			
Coating test						√		
Hydrogen compatibility test	√	√	√	√	√			

2.1.3. Container test results

Container test	Specified design value	Test result
Burst Test		
Ambient Temperature Pressure Cycle Test		
LBB Performance Test		
Bonfire test		
Penetration Test		
Chemical Exposure Test		
Composite Flaw Tolerance Test		
Accelerated Stress Rupture Test		
Extreme Temperature Pressure Cycle Test		
Impact Damage Test		
Leak Test		
Permeation Test		
Boss Torque Test		
Hydrogen Gas Cycling Test		

3. Restriction of use of the device (if any) : None

4. Remarks : None

<sup>(1)</sup> Delete where not applicable.



NOTES:

1.) THE TWO ENDS ARE AVAILABLE IN ANY COMBINATION

NOMINAL PRESSURE RATING: UP TO 35 MPA (5,076 PSI)

MAWP AS TESTED PER EN406: 43.75 MPA (6,345 PSI)

MARKING METHOD: LASER MARKED




TEMPERATURE RATING: (-40C TO +85C)

END 1	END 2
400	400
6MO	6MO
1/4" FEMALE NPT	1/4" FEMALE NPT

SPRING RATES
LOW, MEDIUM, STANDARD

O-RING MATERIAL	COMPOUND
EPDM	Parco 5775-75

ITEM NO.	DESCRIPTION	MATERIAL	QTY.
1	INLET BODY	ASTM A276-316	1
2	OUTLET BODY	ASTM A276-316	1
3	SWAGELOK HARDWARE	ASTM A276-316	2
4	VALVE LABEL	ULTEM HU-3H3D092	1
5	O-RING	SEE O-RING MATERIAL TABLE	1
6	POPPET	ASTM A276-316	1
7	SPRING	ASTM A313-302	1
8	BACKUP RING	PTFE:ASTM D1710-99, TYPE 1, GRADE 1, CLASS B	1



<p>THIS PRINT IS THE EXCLUSIVE PROPERTY OF SWAGELOK COMPANY. IT MUST BE RETURNED ON REQUEST ALONG WITH ANY DOCUMENTS CONTAINING INFORMATION OBTAINED FROM THIS PRINT. NEITHER THIS PRINT NOR ANY PART OF IT NOR ANY INFORMATION CONCERNING IT MAY BE COPIED, DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE EXCEPT IN FURTHERANCE OF YOUR BUSINESS WITH SWAGELOK. THE PARTS REFERRED TO ON THIS PRINT MAY BE THE SUBJECT OF PATENTS AND/OR PENDING APPLICATIONS AND MAY NOT BE MANUFACTURED WITHOUT PERMISSION FROM SWAGELOK COMPANY.</p>	<p>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES .XX ±.01 .XXX ±.005 .XXXX ±.0015 ANGLES ±30 MINUTES INTERPRET DIM. AND TOL. PER ASME Y14.5M-1994</p>	TITLE		APPROVAL/SCHEDULE DRAWING			SHEET		
		MATERIAL		SAP CHANGE NUMBER	DCN-00199925		SCALE	2:1	1 of 1
				DATE	10/16/2020		DWG. NO.	XS FLOW VALVE-EC79-APPROVAL	VS. 00
							REV. -		